




UNCONTROLLED DOCUMENT



NOTES:
 HOLE SIZE: .812
 MAXIMUM PANEL THICKNESS: .125
 MAXIMUM I.D.: .500
 MATERIAL: HEAT STABILIZED NYLON UL 94V2
 STOCKED IN STANDARD BLACK
 TEMPERATURE INDEX: 105° C
 WHITE AVAILABLE UPON REQUEST



TOLERANCES UNLESS NOTED

- ±.005 ON DIMENSIONS THRU .625
- ±.008 ON DIMENSIONS .626 THRU 1.000
- ±.010 ON DIMENSIONS 1.001 THRU 1.500
- ±.015 ON DIMENSIONS LARGER THAN 1.500
- ±.015 ON FRACTIONAL DIMENSIONS

WE RESERVE THE RIGHT TO
 DISCONTINUE ITEMS, CHANGE
 SPECIFICATIONS OR DESIGN AT
 ANY TIME WITHOUT NOTICE AND
 WITHOUT INCURRING ANY OBLIGATIONS

PROPERTY OF

MICRO PLASTICS INC.

CATALOG DRAWING
 MICRO P/N 22AF0812
 DWG. # 22AF0812
 FILE SERVER/ENG/CAT

MATERIAL: SEE NOTES

SCALE

3:1

JDD