

**Cabtite (cable entry system)
CABTITE FRL 24/10 BK**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com



The frame, fabricated from a single piece, is quick and easy to assemble and consists of dimensionally stable, fibre-glass reinforced plastic. The captive foamed seal guarantees effective IP66 sealing in accordance with DIN EN 60529, even on painted and rough surfaces.

General ordering data

Type	CABTITE FRL 24/10 BK
Order No.	2584210000
Version	Cable entry systems, Cabtite (cable entry system), Polyamide, glass fibre-reinforced, Deep black, Height: 11.3 mm, Width: 68.8 mm, Depth: 11.3 mm, -40 °C...120 °C
GTIN (EAN)	4050118615289
Qty.	10 pc(s).

Cabtite (cable entry system)
CABTITE FRL 24/10 BK

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data**Dimensions and weights**

Length	152 mm	Length (inches)	5.984 inch
Width	68.8 mm	Width (inches)	2.709 inch
Height	11.3 mm	Height (inches)	0.445 inch
Height of lowest version	11.3 mm	Depth	11.3 mm
Depth (inches)	0.445 inch	Mounting dimension - width	32 mm
Mounting dimension - height	130 mm	Net weight	37.1 g
Diameter	5.5 mm		

General information

Tightening torque	3 Nm	Opening width	40 mm
Opening length	107.5 mm	UL 94 flammability rating	V-0
Halogen	No	Silicone	No
Material	Polyamide, glass fibre-reinforced		

Classifications

ETIM 6.0	EC002624	eClass 6.2	27-14-92-01
eClass 9.1	27-18-92-65		

Approvals

Approvals



ROHS Conform

DownloadsUser Documentation [CabTite Installation Instructions](#)