

**ModuPlug  
HDC MRJ45 GC F**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com

**Flexible**

The four module sizes make for individual plug solutions that save a huge amount of space. The smaller pitch translates into an optimised design too.

**General ordering data**

Type	HDC MRJ45 GC F
Order No.	<a href="#">2592030000</a>
Version	Module, RJ45 Gender Changer
GTIN (EAN)	4050118600506
Qty.	1 pc(s).

**ModuPlug  
HDC MRJ45 GC F**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

**Technical data****Dimensions and weights**

Net weight	5.5 g
------------	-------

**Temperatures**

Limit temperature	-40 °C ... 70 °C
-------------------	------------------

**Environmental Product Compliance**

REACH SVHC	Potassium perfluorobutane sulfonate 29420-49-3
------------	--

**General data**

Insulating material	PC glass-fibre reinforced (UL-listed and railway-certified)	Insulation strength	10 <sup>12</sup> Ω
Material	Polycarbonate, glass fibre reinforced	Number of poles	8
Plugging cycles	750 (RJ45)	Pollution severity	3
Rated current (DIN EN 61984)	1 A	Rated impulse voltage (DIN EN 61984)	0.8 kV
Rated voltage (DIN EN 61984)	50 V	Required plug-in slots	1
Series	ModuPlug	Surge voltage category	III
Type	Pin	UL 94 flammability rating	V-0

**Classifications**

ETIM 6.0	EC002312	ETIM 7.0	EC002312
eClass 9.0	27-44-02-92	eClass 9.1	27-44-02-18
eClass 10.0	27-44-02-92		

**Downloads**

Engineering Data	<a href="#">STEP</a>
------------------	----------------------