Weidmüller ⯎

IE-FC-SET-SP-US-D008-KN-4X

FrontCom® Vario integrates multiple functions in only
one single frame. The system is easy to install and
you can select from a wide range of data, signal and
power modules. In addition to being extremely compact,
FrontCom® Vario offers a number of unique product
features that will make your project planning and work
activities secure, fast and future-proof. Furthermore,
the FrontCom® Vario system has an attractive housing
design that, by the way, offers highest impact-resistance
and fully meets the requirements of IP 65 protection
class.

General ordering data

Version	FrontCom
Order No.	7940111827
Type	IE-FC-SET-SP-US-D008-KN-4X
GTIN (EAN)	4064675115670
Qty.	1 pc(s).
Reference product	2669640000 2003370000 1487920000 1962840000

Creation date August 23, 2023 9:53:35 AM CEST

Weidmüller ⧉

IE-FC-SET-SP-US-D008-KN-4X

Technical data

Dimensions and weights

Net weight	1,187 g

General data

Protection class (UL)	NEMA 4X	Protection degree	IP65, in closed state

Technical data

Data inserts	RJ45 coupling Cat.6$_A$, USB 3.0 A/A	Frame	Metal cover, NEMA 4X
Insert plate	2x data, 1x signal, 1x fuse, 1x GFCI, Unshielded	Rated current for socket	20 A
Rated voltage for socket	125 V		

Classifications

ETIM 6.0	EC001031	ETIM 7.0	EC001031
ETIM 8.0	EC001031	ECLASS 9.0	27-18-27-02
ECLASS 9.1	27-18-27-90	ECLASS 10.0	27-18-27-02
ECLASS 11.0	27-18-27-02	ECLASS 12.0	27-18-28-92

Environmental Product Compliance

REACH SVHC	Potassium perfluorobutane sulfonate 29420-49-3

Important note

Product information	All components in this set have UL approval. For more details please check the reference products that are included in the kit.

Approvals

ROHS	Conform

Downloads

Catalogues	[Catalogues in PDF-format](#)

Creation date August 23, 2023 9:53:35 AM CEST