






THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.

REV.	ECN NO.	DATE	SIGN	DESCRIPTION
C	C201393	2020-09-10	Allen Pan	$\triangle C$ X1
D	C220438	2022-03-21	Ruru	$\triangle D$ X4
E	C230124	2023-02-06	Ruru	$\triangle E$ X1



AB-AUXXXFL-UPBML-QHXXX  
 $\triangle$  XX: No. Of Pin  
 $\triangle B$  XXX: 0.5~40Meters  
 A05: 0.5Meter  
 001: 01Meter  
 002: 02Meters  
 ...  
 $\triangle B$  040: 40Meters

Note:  $\triangle$   
 \* RoHS Compliant  
 \*  $\odot$  Important dimension  
 \* C1  
 Waterproof rate: IP68, mated 1m/24h  
 Housing: Thermoplastic, Black  
 Pin: Copper Alloy, Gold Plated  
 O-Ring: Rubber, Black  
 Nut: Thermoplastic, Black  
 Outer mold: Thermoplastic, Black  
 \* C2  
 Waterproof rate: Non-Waterproof  
 Plug: RJ45, Shielded  
 $\triangle C$  \* Cable: CAT-5E, UTP, 24#\*4P,  
 OD=6mm, PVC Jacket, Black  
 \* Cable length tolerance  
 0.5M < L ≤ 1M: +60/-0 mm  
 1M < L ≤ 3M: +120/-0 mm  
 3M < L ≤ 5M: +160/-0 mm  
 5M < L ≤ 10M: ±100 mm  
 10M < L ≤ 20M: ±200 mm  
 20M < L ≤ 30M: ±300 mm  
 30M < L ≤ 40M: ±500 mm

$\triangle B$	$\triangle B$	$\triangle B$	$\triangle B$	
3	Brown	棕	8	Twist 對線
2	White/Brown	白/棕	7	
8	Green	綠	6	Twist 對線
5	White/Green	白/綠	3	
7	Blue	藍	4	Twist 對線
1	White/Blue	白/藍	5	
4	Orange	橘	2	Twist 對線
6	White/Orange	白/橘	1	
C1	Wire Color		C2	

UNIT: mm   
 TOLERANCE  
 ±0.5 mm

TITLE  
 ACC, XLOK, A-2A, DB-ENDED  
 FM  $\triangle D$   
 SCALE Free SHEET 1 OF 1  
 REV. E SIZE A4  $\odot$ : Inspection Item

**Amphenol LTW**  
 安費諾亮泰企業股份有限公司

ITEM NO	DRAWN BY Allen Pan	DATE 2020-03-16
DWG NO AB-AUXFL-UPBML-QHXXX $\triangle D$	CHECKED BY Sam Ho	DATE 2020-03-16
CUSTOMER ALTW	APPROVED BY Fred Lee	DATE 2020-03-16