

Botron Digital & Analog Surface Test Kit **B8572** is an easy to read a large digital and analog megohm tester. Test up to 100Gegohms (see spec). Also has a (Quick Check) megohm scale on faceplate from $>10^4$ to $<10^{11}$ range. Select the desired test range and push the large test button for reading, you may also lock-in your test results by pushing the yellow lock button. When in a low light condition press yellow back-light button. The Auto shut-off feature will conserve the battery life. Optional transducer to test humidity & temperature is available. **Disclaimer:** All statements of technical information are believed to be true and are based upon tests we believe to be reliable. The proper use and application for this product must be the responsibility of the user. The statements herein shall have no force or effect.

No need for separate voltage tester. This will test voltage and continuity.



Insert six (6) AA batteries into compartment on back of tester. Plug test leads in jacks on tester, plug other end into hole on 5 lbs weight. Select test voltage 10volts or 100 volts or 500 if needed. For test below $<10^6$ use 10volts for test over $>10^6$ use 100volts. Press and hold test button, when analog needle stops that will be your analog reading and the digital reading will stay on in megohm's. With it's large digital display and instant reading on the analog scale you will be able to test much faster and more accurately than many other megohm meters on the market today. This unit has three ways to read a test **1.** Analog, **2.** Digital **3.** 10^3 - 10^{11} ohms scale on the faceplate

PROPERTIES

Test Range: 100G/100v 100G/500v Analog
20G/100v Digital
Auto Shut off: Conserve battery
Locking Test: As needed
Electrodes: Two (2) 5lbs weights
Read out: Digital & Analog (instantly)
Test Voltage: 10v, 100v & 500volts
Low battery: Symbol
Millivolt Test: +/- 1m-1999mV
Voltage Test: 500volts
Water Resistant: IP54
Dust Proof: IP54
Designed to: IEC1010-1
Warranty: Three (3) years
Back Light: Auto shut off
Microprocessor: Controlled
Case: Foam filled

SPECIFICATIONS

100G/100v 100G/500v Analog
20G/100v Digital
Conserve battery
As needed
Two (2) 5lbs weights
Digital & Analog (instantly)
10v, 100v & 500volts
Symbol
+/- 1m-1999mV
500volts
IP54
IP54
IEC1010-1
Three (3) years
Auto shut off
Controlled
Foam filled

OTHER PRODUCTS:

B8201 Touch plate wrist strap Tester
B8511 Combo tester, wrist & heel
B82450 Combo testers & stand
B82250 Dual tester & stand
B85501 Wrist Calibration unit
B85502 Combo Calibration unit
B8202 Wrist tester
B8525 Deluxe dual test station

Complete your Auditing Test Kit with a Digital Field meter **B48775**; Not included in Digital /Analog Test kit, must be ordered separately.



B48775

RELATED TEST EQUIPMENT:

B8563 Analog Megohm meter
B8562 LED 100v Megohm meter
B8562KIT LED 100v Megohm meter and weights
B8560 SRM Megohm meter 9v
B9201 Constant monitor
B9202 Constant monitor
BSRM-10 10 light surface meter
BSRM-6 6 light surface meter.

BOTRON CO. INC.

325 W. MELINDA LN

PHOENIX AZ 85027

PH# 623-582-6700 FAX# 623-582-6776

DIGITAL & ANALOG MEGGER OHM TEST KIT

S8572

sales@botron.com / www.botron.com