


THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.

REV.	ECN NO.	DATE	SIGN	DESCRIPTION
C	C210025	2021/01/19	Vicky	$\triangle C$ X1
D	C210497	2021/03/30	Ruru	$\triangle D$ X2
E	C222002	2022/12/29	Ruru	$\triangle E$ X1




Note:  $\triangle B$   $\triangle C$   $\triangle D$

- \* RoHS Compliant
- \*  $\odot$  Important dimension
- $\triangle E$  \* Waterproof rate: IP68, mated 1m/24h  
IP69K, mated
- \* Connector:  
Housing: Thermoplastic, Black  
Pin: Copper alloy, Gold plated  
Nut: Metal  
Outer mold: Thermoplastic, Black
- \* Cable: UL20549, 22#\*4C, OD=4.0mm, PUR Jacket, Black
- \* Cable length tolerance: 0.5M < L ≤ 1M: +60/-0 mm  
1M < L ≤ 3M: +120/-0 mm  
3M < L ≤ 5M: +160/-0 mm  
5M < L ≤ 10M: ±100 mm  
10M < L ≤ 20M: ±200 mm  
20M < L ≤ 30M: ±300 mm  
30M < L ≤ 99M: ±500 mm

$\triangle B$  MI2DXXML-12DML-SBXXX  
 XX: No. Of Pin  
 XXX: 0.5~99Meters  
 A05: 0.5 Meter  
 001: 1 Meter  
 002: 2 Meters  
 :  
 099: 99 Meters

Pin Out	Wire	Color
5	--	
4	Black	黑
3	Blue	藍
2	White	白
1	Brown	棕



Pin Assignments Front View

UNIT:mm	$\varnothing$
TOLERANCE	±0.5 mm

TITLE ACC, SEN, D Code, DB-ENDED MM $\triangle D$			
SCALE 1:2	SIZE A4	SHEET 1 OF 1	
REV. E	WC-REV. A.5	$\odot$ : Inspection item	

**Amphenol LTW**  
 安費諾亮泰企業股份有限公司

ITEM NO	DRAWN BY Vicky	DATE 2018-12-11
DWG NO $\triangle A$ MI2DXXML-12DML-SBXXX	CHECKED BY Rita	DATE 2018-12-11
CUSTOMER ALTW	APPROVED BY Max	DATE 2018-12-11