


REV.	ECN NO.	DATE	SIGN	DESCRIPTION
B	LEN1660925~928	2016/06/22	Vicky	Update Logo





Cable ②

12P-05BFFM-SL8000 ①
Color: Black

MCP-05BFFM-SL8AXX

XX:01~99Meters
 01:01Meter
 02:02Meters
 :
 :
 99:99Meters
 Cable Length(L):01~99Meters



Pin Assignments
Front View

5	Blue	(24AWG)	Twist
4	White	(24AWG)	
3	Black	(22AWG)	Twist
2	Red	(22AWG)	
1	Shield	(22AWG)	
Conn.	Wire Color		
	Pin Out		

- Note:
- * Ⓞ Important Dimension.
 - * Waterproof Rate: IP68
IP68: 1M Depth Of Water In 24hours
 - * Connector: Polyurethane (PU), Black
 - * Female Pin: Copper Alloy, Gold Plated
 - * Cable: (24AWG*1P+Al)+(22AWG*1P+Al)+Drain +Al.Mylar+Braid, OD=6.0mm, Black
 - * Cable Length Tolerance: 1M:±40mm
 02M~05M:±60mm
 06M~10M:±100mm
 11M~30M:±200mm
 31M~99M:±500mm

UNIT:mm	
TOLERANCE	±0.5 mm

TITLE		M12P Conn NMEA	
Cable Screw 5Pin F Conn F Pin			
SCALE	Free	SHEET	1 OF 1
REV.	B	SIZE	A4
Ⓞ :Inspection Item			

Amphenol LTW
安費諾亮泰企業股份有限公司

ITEM NO	DRAWN BY	DATE
	Vicky	2016/06/22
DWG NO	CHECKED BY	DATE
MCP-05BFFM-SL8AXX	Rita	2016/06/22
CUSTOMER	APPROVED BY	DATE
ALTW	Lisa	2016/06/22

THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.