


THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.


REV.	ECN NO.	DATE	SIGN	DESCRIPTION
B	C210337	2021/03/08	Vicky	Old Item No. MSXSXXML-SXSML-SGXXX
C	C220546	2202/03/31	Arvin Chan	$\triangle C$ X1
D	C222002	2202/12/30	Ruru	$\triangle D$ X2



MSXSXXML-SXSML-SXXXX
 XX: No. Of Pin
 XXX: 0.5-40Meters
 A05: 0.5 Meter
 001: 01 Meter
 002: 02 Meters
 ...
 040: 40 Meters

- Note:
- * RoHS Compliant
 - * ⌀ Important dimensions
 - $\triangle D$ * Waterproof rate: IP67, mated
 - * Connector
 Housing: Thermoplastic, Black
 Pin: Copper alloy, Gold plated
 Nut: Metal
 Outer Mold: Thermoplastic, Black
 - $\triangle C$ * Cable: CAT-6A, 26AWG*4P+AL/MY+B,
 TPU Jacket, OD 6.8mm, Green
 - * Cable Length Tolerance: 0.5M < L ≤ 1M: +60/-0 mm
 1M < L ≤ 3M: +120/-0 mm
 3M < L ≤ 5M: +160/-0 mm
 5M < L ≤ 10M: ±100 mm
 10M < L ≤ 20M: ±200 mm
 20M < L ≤ 30M: ±300 mm
 30M < L ≤ 100M: ±500 mm

Shield	Braid	編織	Shield	
8	Blue	藍	8	Twist
7	White/Blue	白/藍	7	
6	Brown	棕	6	Twist
5	White/Brown	白/棕	5	
4	Green	綠	4	Twist
3	White/Green	白/綠	3	
2	Orange	橘	2	Twist
1	White/Orange	白/橘	1	
C1	Wire Color		C2	



UNIT:mm	⌀ ⌀	TITLE	ACC, SEN, X Code, DB-ENDED MM $\triangle D$		
TOLERANCE	± 0.5 mm	SCALE	I:1	SIZE	A4
		REV.	D	WC-REV.	A.3
			⌀ : Inspection item		

Amphenol LTW
 安費諾亮泰企業股份有限公司

ITEM NO	DRAWN BY	DATE
DWG NO	CHECKED BY	DATE
CUSTOMER	APPROVED BY	DATE
ALTW	Vicky Rita Max	2021-02-24 2021-02-24 2021-02-24