


REV.	ECN NO.	DATE	SIGN	DESCRIPTION
A		2020/08/07	Eric	Initial Release
B	C201246	2020/08/12	Eric	Δ B x1

THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.



UA20FL-UAFL-SAXXX
 A05 : 0.5 Meters
 001 : 01 Meter
 002 : 02 Meters
 :
 :
 005 : 05 Meters
 Cable Length : 01~05Meters

NOTE:
 * \textcircled{C} Important Dimension
 * Waterproof Rate: IP67
 * Connector: USB2.0-A Male Solder
 * Cable: USB 2.0 28AWG*1P+24AWG*2C+AL/MY+D+B
 Black, PVC Jacket, UV Resistance, OD=5.0mm
 Δ * Cable Length Tolerance: 0.5M: ± 60 mm
 01M-03M: $\begin{matrix} +120 \\ -0 \end{matrix}$ mm
 04M,05M: $\begin{matrix} +160 \\ -0 \end{matrix}$ mm

Shield	Drain	28AWG	地線	Shield
4	Black	24AWG	黑	4
3	Green	28AWG	綠	3
2	White	28AWG	白	2
1	Red	24AWG	紅	1
C1	Wire Color			C2

Pin Out

Twist

UNIT: mm		TITLE
TOLERANCE		USB, A TYPE, 2.0, CABLE W/O SR
± 0.5 mm		
SCALE	Free	SHEET 1 OF 1
REV. B	SIZE A4	\textcircled{C} : Inspection Item

Amphenol LTW
 安費諾亮泰企業股份有限公司

ITEM NO	UA20FL-UAFL-SAXXX	DRAWN BY	Eric	DATE	2020/08/07
DWG NO	UA20FL-UAFL-SAXXX	CHECKED BY	Brady	DATE	2020/08/07
CUSTOMER	ALTW	APPROVED BY	Neo	DATE	2020/08/07