



THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.

REV.	ECN NO.	DATE	SIGN	DESCRIPTION
A	Initial Released	2020/08/21	Ruru	Old Item No. UA-30BFM-SD7BXX



UA30FL-NAML-SBXXX  
 XXX : 01~03Meters  
 001 : 01Meter  
 002 : 02Meters  
 ...  
 003 : 03Meters  
 Cable Length(L): 01~03Meters

Note:  
 \*  $\varnothing$  Important Dimension To Check.  
 \* Waterproof Rate: IP67  
 \* Jack: USB3.0-A Male Solder  
 \* Gasket: Rubber, Black  
 \* Screw Nut: Thermoplastic, Black  
 \* Cable: UL2725(IPx28#+DAM)\*2+1P\*28#+2C\*28#+ABD, PVC Jacket, UV Resistant, OD=6.0mm, Black  
 \* Cable Length Tolerance: 01M: 40mm  
 02M~03M: ±60mm  
 \* All of Drain twisted together.



Pin Assignments  
Front View

Shield	Braid	編織	Shield	Shield	
9	Orange	28AWG 橙	SDP2+	9	Twist
8	Purple	28AWG 紫	SDP2-	8	
7	Drain	28AWG	SDP2_Drain	7	Twist
6	Yellow	28AWG 黃	SDP1+	6	
5	Blue	28AWG 藍	SDP1-	5	Twist
7	Drain	28AWG	SDP1_Drain	7	
4	Black	28AWG 黑	GND_PWRrt	4	Twist
3	Green	28AWG 綠	UTP_D+	3	
2	White	28AWG 白	UTP_D-	2	Twist
1	Red	28AWG 紅	PWR	1	
Conn.1	Wire Color		Signal Name	Conn.2	

Pin Out

UNIT:mm		
TOLERANCE	±0.5	

TITLE ACC, USB, A TYPE, DB-ENDED, FM			
SCALE 1:1	SIZE A4	SHEET 1 OF 1	
REV. A	WC-REV. A.5	$\varnothing$ : Inspection item	

**Amphenol LTW**  
 安費諾亮泰企業股份有限公司

ITEM NO.	DRAWN BY Ruru	DATE 2020-08-21
DWG NO. UA30FL-NAML-SBXXX	CHECKED BY Rita	DATE 2020-08-21
CUSTOMER ALTW	APPROVED BY Max	DATE 2020-08-21