



THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF AMPHENOL LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY AMPHENOL LTW.

REV.	ECN NO.	DATE	SIGN	DESCRIPTION
A	Initial Released	2020/08/24	Ruru	Old Item No. UC-20AMM-QA8AXX
B	C220034	2022/01/24	Zhi Cheng	\triangle B *1



MA 8.0

Shield	Braid	編織	Shield
4	Black	黑	B12
			B1
			A12
			A1
3	Green	綠	A6
2	White	白	A7
1	Red	紅	B9
			B4
			A9
			A4
Conn. 2	Wire Color		Conn. 1
Pin Out			

UC20ML-NAML-QAXXX
 XXX: 01~03 Meters
 001: 1 Meter
 002: 2 Meters
 003: 3 Meters
 Cable Length tolerance: 1~3M±50mm

- Note:
- * \varnothing Important Dimension
 - * Conn.1: USB Type C, Plug
 - * Housing: Thermoplastic, UL94 V-0, Black
 - * Gasket: Rubber, Black
 - * Waterproof Rate: IP68(Mated)(under water, 1M, 24H)
 - * Conn.2: USB Type A 2.0, Plug
 - * Non-waterproof
 - * Cable: UL2725 32AWG*2C+24AWG*1C+28AWG*1C+D+A1/My+B PVC Jacket, OD=2.8mm, Black

UNIT: mm TOLERANCE ± 0.5	TITLE ACC, USB, C TYPE, DB-ENDED, MM		Amphenol LTW 安費諾亮泰企業股份有限公司		ITEM NO	DRAWN BY Ruru	DATE 2020-08-24
	SCALE 1:1	SIZE A4			SHEET 1	OF 1	DWG NO UC20ML-NAML-QAXXX
	REV. B	WC-REV. .0	\varnothing : Inspection item	CUSTOMER ALTW	APPROVED BY Max	DATE 2020-08-24	