

Detailed Specifications

Frame Width:	60[mm]
Frame Height:	60[mm]
Frame Depth:	38[mm]
Max. Air Flow:	73.1[CFM]
Max. Air Flow:	2.07[m3 per min]
Max. Static Pressure:	3.56[In H2O]
Max. Static Pressure:	887[Pa]
Fan Speed:	17000[RPM]
Noise:	66.5[dB]
Life Expectancy:	40 degrees C 70,000 Hours[L10]
Bearing Type:	Ball Bearing
Speed Control:	PWM
Nominal Voltage:	12[V]
Operating Voltage - Lower:	10.8[V]
Operating Voltage - Upper:	13.2[V]
Mass:	125[g]
Tach / Locked Rotor Output:	Tach Output
Status:	Active

PWM Speed Control Fans