



Virtually Indestructible (3)D LED Lantern DIYLN3D-BXB



RAYOVAC® Virtually Indestructible (3)D LED Lantern

- 600 lumens
- Two Modes: High and Energy Saver
- 15ft Drop Tested – Shatterproof Lens and Reflector, Hang Hook, Top Handle, Easy Push On/Off Switch
- Waterproof/Submersible & Dustproof (ANSI IP67)
- Includes (3)D RAYOVAC® High Energy Batteries
- Lifetime Warranty

Description:	RAYOVAC® Virtually Indestructible (3)D LED Lantern
Item UPC:	12800519835
Item Dimensions (in) (L x W x H):	4.375 x 4.000 x 10.000
Item Weight (lbs) :	2.760
Item Cube (ft³):	0.101
Case UPC:	10012800519832
Case Dimensions (in) (L x W x H):	9.125 x 8.750 x 10.500
Case Weight (lbs) :	11.705
Case Cube (ft³) :	0.485
Case Quantity:	4
Ti X Hi= (cases/pallet):	20 x 4 = 80
Bulb:	LED
Battery Size:	3D
Package Style:	Peggable/Free Standing
Lumens:	600 on high / 68 on low
Runtime (hours):	40 on high / 260 on low
Beam Distance (meters):	13 on high / 4.5 on low
EDLP	\$29.99
Hi/Lo	\$34.99

Package UPC:



Case UPC:

