









RoHS COMPLIANT

REV	DATE	DESCRIPTION
A	11/01/'23	(Official Drawing)



NO.	CC+ P/N	Internal P/N	ITEM P/N	DESCRIPTION	Q'TY	UNIT	PRODUCT PACKING
1	DCT-15HMMD-KIT	HH-15PKC00PA	HH-15PKC00B0	D-SUB HD 15PIN CRIMP TYPE MALE	1	PCS	BIG BAG:10.5*10*0.05CM
			HT-PAAAA0	HD CRIMP TYPE MALE TERMINAL	15	PCS	
			CM7-09ADFG0AA0	D-SUB 09PIN METAL HOOD OD:7.5MM	1	SET	
			XG09-15	GROMET	1	PCS	
2	DCT-15HFMD-KIT	HH-15SKC00PA	HH-15SKC00B0	D-SUB HD 15PIN CRIMP TYPE FEMALE	1	PCS	BIG BAG:10.5*10*0.05CM
			HT-SAAAA0	HD CRIMP TYPE FEMALE TERMINAL	15	PCS	
			CM7-09ADFG0AA0	D-SUB 09PIN METAL HOOD OD:7.5MM	1	SET	
			XG09-15	GROMET	1	PCS	

NOTE:

WARNING
Cancer and Reproductive Harm
www.P65Warnings.ca.gov

CompuCableUSA

MODEL NAME:
Crimp Type Deluxe Shielded Metal
Hood Kit

MARK EXPLAIN:
A:Revision Change
I:Important Dimension
①:Note

TOLERANCE:
0.00:
0.00 : ±0.20
0.0 : ±0.30
0. : ±0.40
ANGLE: ±3.0°

PART NO. DCT-15HXMD-KIT

APPROVED BY: ARISA

CHECKED BY: ALAN

DRAW BY: ALAN

FILE NO. FIG03404

SCALE: 1/1

DATE: 1121101