

H25,0/15**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



For conductors from 10.0 to 185.0 mm² (AWG 7 - 350 MCM)

tin-plated copper

dimensional tolerances to DIN 46228 part 1

- supplied loose in poly-bag

General ordering data

Version	Wire-end ferrule, Standard, 15 mm, 15 mm, No
Order No.	0124400000
Type	H25,0/15
GTIN (EAN)	4008190071790
Qty.	250 pc(s).
Packaging	loose

Creation date February 5, 2024 10:58:54 AM CET

Catalogue status 27.01.2024 / We reserve the right to make technical changes.

H25,0/15**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data**Dimensions and weights**

Net weight 0.62 g

Technical data

Description of article	Wire end ferrule without plastic collar	Version	Standard
------------------------	---	---------	----------

Wire-end ferrules

Collar diameter (D2)	9.5 mm	Conductor cross-section	25 mm ²
Contact surface diameter (D1)	7.3 mm	Contact surface length (L2)	15 mm
L1 in mm	15 mm	Stripping length	15 mm
Wire connection cross section AWG, max.	AWG 3		

Classifications

ETIM 6.0	EC000005	ETIM 7.0	EC000005
ETIM 8.0	EC000005	ETIM 9.0	EC000005
ECLASS 9.0	27-40-02-01	ECLASS 9.1	27-40-02-01
ECLASS 10.0	27-40-02-01	ECLASS 11.0	27-40-02-01
ECLASS 12.0	27-40-02-01	ECLASS 13.0	27400201

Approvals

Approvals



ROHS Conform

UL File Number Search UL Website

Certificate no. (cULus) E499744

DownloadsEngineering Data [CAD data – STEP](#)Engineering Data [Zuken E3.S](#)Catalogues [Catalogues in PDF-format](#)

Brochures

Data sheet

H25,0/15

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

