

**AP SAKS1+3 KRG****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Product image**

AP 019132



End plates are fitted to the open side of the last modular terminal before the end bracket. The use of an end plate ensures the function of the modular terminal and the specified rated voltage. It guarantees protection against contact with live parts and makes the final terminal finger-proof.

**General ordering data**

|            |  |
|------------|--|
| Version    | SAK Series, End plate, 3 mm, dark beige, yellow, Direct mounting |
| Order No.  | <a href="#">0191320000</a>                                       |
| Type       | AP SAKS1+3 KRG   |
| GTIN (EAN) | 4008 19003 1688  |
| Qty.       | 20 pc(s).  |

Creation date February 5, 2024 11:04:32 AM CET

Catalogue status 27.01.2024 / We reserve the right to make technical changes.

## AP SAKS1+3 KRG

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

### Dimensions and weights

|            |       |                 |            |
|------------|-------|-----------------|------------|
| Depth      | 36 mm | Depth (inches)  | 1.417 inch |
| Height     | 54 mm | Height (inches) | 2.126 inch |
| Width      | 3 mm  | Width (inches)  | 0.118 inch |
| Net weight | 7.4 g |                 |            |

### Temperatures

|                                  |                |                                  |        |
|----------------------------------|----------------|----------------------------------|--------|
| Storage temperature              | -25 °C...55 °C | Continuous operating temp., min. | -60 °C |
| Continuous operating temp., max. | 130 °C         |                                  |        |

### Material data

|                           |     |        |                    |
|---------------------------|-----|--------|--------------------|
| Material                  | KrG | Colour | dark beige, yellow |
| UL 94 flammability rating | V-0 |        |                    |

### System specifications

|         |           |
|---------|-----------|
| Version | End plate |
|---------|-----------|

### Additional technical data

|                     |                 |         |     |
|---------------------|-----------------|---------|-----|
| Installation advice | Direct mounting | Snap-on | Yes |
|---------------------|-----------------|---------|-----|

### General

|                     |                 |
|---------------------|-----------------|
| Installation advice | Direct mounting |
|---------------------|-----------------|

### Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC000886    | ETIM 7.0    | EC000886    |
| ETIM 8.0    | EC000886    | ETIM 9.0    | EC000886    |
| ECLASS 9.1  | 27-14-11-33 | ECLASS 10.0 | 27-14-11-33 |
| ECLASS 11.0 | 27-14-11-33 | ECLASS 12.0 | 27-14-11-33 |
| ECLASS 13.0 | 27250301    |             |             |

### Approvals

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

### Downloads

|                    |   |
|--------------------|---|
| User Documentation | <a href="#">StorageConditionsTerminalBlocks</a> |
| Catalogues         | <a href="#">Catalogues in PDF-format</a>        |