

## H0,75/10

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)



For conductors from 0.25 to 6,0 mm<sup>2</sup> (AWG 24 - 10)  
tin-plated copper  
dimensional tolerances to DIN 46228 part 1

- supplied loose in polybag

### General ordering data

Version	Wire-end ferrule, Standard, 10 mm, 10 mm, No
Order No.	<a href="#">0542500000</a>
Type	H0,75/10
GTIN (EAN)	4008 190037482
Qty.	1,000 pc(s).
Packaging	loose

Creation date February 5, 2024 10:31:09 AM CET

Catalogue status 27.01.2024 / We reserve the right to make technical changes.

**H0,75/10****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Technical data****Dimensions and weights**

Net weight 0.06 g

**Technical data**

Description of article	Wire end ferrule without plastic collar	Version	Standard
------------------------	---	---------	----------

**Wire-end ferrules**

Collar diameter (D2)	2.3 mm	Conductor cross-section	0.75 mm <sup>2</sup>
Contact surface diameter (D1)	1.2 mm	Contact surface length (L2)	10 mm
L1 in mm	10 mm	Stripping length	10 mm
Wire connection cross section AWG, max.	AWG 18		

**Classifications**

ETIM 6.0	EC000005	ETIM 7.0	EC000005
ETIM 8.0	EC000005	ETIM 9.0	EC000005
ECLASS 9.0	27-40-02-01	ECLASS 9.1	27-40-02-01
ECLASS 10.0	27-40-02-01	ECLASS 11.0	27-40-02-01
ECLASS 12.0	27-40-02-01	ECLASS 13.0	27400201

**Approvals**

Approvals



ROHS Conform

UL File Number Search UL Website

Certificate no. (cULus) E499744

**Downloads**Engineering Data [CAD data – STEP](#)Engineering Data [Zuken E3.S](#)Catalogues [Catalogues in PDF-format](#)

Brochures

**Data sheet**

**H0,75/10**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Drawings**

