

VQB 1.5/50 BL**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Product image

Numerous national and international approvals and qualifications in accordance with a variety of application standards make the W-series a universal connection solution, especially in harsh conditions. The screw connection has long been an established connection element to meet exacting demands in terms of reliability and functionality. And our W-Series is still setting standards.

General ordering data

| | |
|------------|--|
| Version | SAK Series, Cross-connector bridge, for cross-connection link, Number of poles: 50 |
| Order No. | 1633280000 |
| Type | VQB 1.5/50 BL |
| GTIN (EAN) | 4008 190257743 |
| Qty. | 5 pc(s). |

Creation date February 5, 2024 10:56:11 AM CET

Catalogue status 27.01.2024 / We reserve the right to make technical changes.

VQB 1.5/50 BL

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Dimensions and weights

| | | | |
|------------|----------|-----------------|-------------|
| Depth | 12.85 mm | Depth (inches) | 0.506 inch |
| Height | 306.1 mm | Height (inches) | 12.051 inch |
| Width | 4.2 mm | Width (inches) | 0.165 inch |
| Net weight | 16.8 g | | |

Temperatures

| | |
|---------------------|----------------|
| Storage temperature | -25 °C...55 °C |
|---------------------|----------------|

Material data

| | |
|--------|------|
| Colour | blue |
|--------|------|

System specifications

| | |
|---------|---------------------------|
| Version | for cross-connection link |
|---------|---------------------------|

Additional technical data

| | | | |
|--------------------------|-----------------|---------------------|-----------------|
| Explosion-tested version | No | Installation advice | Direct mounting |
| Type of fixing | when screwed in | | |

Dimensions

| | |
|-----------------|--------|
| Pitch in mm (P) | 6.2 mm |
|-----------------|--------|

General

| | | | |
|---------------------|-----------------|-----------------|----|
| Installation advice | Direct mounting | Number of poles | 50 |
|---------------------|-----------------|-----------------|----|

Rating data

| | |
|---------------|--------|
| Rated current | 17.5 A |
|---------------|--------|

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC000489 | ETIM 7.0 | EC000489 |
| ETIM 8.0 | EC000489 | ETIM 9.0 | EC000489 |
| ECLASS 9.0 | 27-14-11-40 | ECLASS 9.1 | 27-14-11-40 |
| ECLASS 10.0 | 27-14-11-40 | ECLASS 11.0 | 27-14-11-40 |
| ECLASS 12.0 | 27-14-11-40 | ECLASS 13.0 | 27250303 |

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Downloads

| | |
|--------------------|---|
| Engineering Data | CAD data – STEP |
| Engineering Data | Zuken E3.S |
| User Documentation | Beipackzettel_VQB1.5.pdf StorageConditionsTerminalBlocks |
| Catalogues | Catalogues in PDF-format |
| Brochures | |

Creation date February 5, 2024 10:56:11 AM CET

Catalogue status 27.01.2024 / We reserve the right to make technical changes.