

REV	DESCRIPTION	DATE	APPROVED
A			
B			
C			





TABLE 1

LENGTH	TOLERANCE
<.5m	±1cm
.5m TO 2m	±5cm
2m TO 5m	±10cm
>5m	±15cm

WIRE LIST

PIN	PAIR	TWISTED PAIR COLOR	SIGNAL	IND. BANANA COLOR	PLUG
1	1	BLACK	AB0-	BLACK	P3
2	1	RED	AB0+	RED	P2
3	2	GREEN	AB1-	BLACK	P5
4	2	WHITE	AB1+	RED	P4
STANDOFF (ITEM 6)	-	-	DRAIN	-	NO CONNECT

CUSTOMER DRAWING

NATIONAL INSTRUMENTS®

TITLE: TYPE HV6 TO BANANA (4X)  
192795-0R2

SIZE: 192795-0R2  
DRAWING NO. 04/03/19

SCALE: NTS

DO NOT SCALE DRAWING  
THIRD ANGLE PROJECTION

UNLESS SPECIFIED OTHERWISE DIMENSIONS ARE IN INCHES AND MILLIMETERS

AUSTIN, TEXAS

1. REFER TO PRODUCT MANUAL ON NI.COM FOR MORE DETAILS.  
NOTES: UNLESS OTHERWISE SPECIFIED.