

**G 20/6.30A/F****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Product image**

Similar to illustration

For protection against overcurrent, we offer cartridge fuse with dimensions 5x20 mm in sizes from 100 mA to 6.3 A.

**General ordering data**

|            |                            |
|------------|----------------------------|
| Version    | Active components, Fuse    |
| Order No.  | <a href="#">0431400000</a> |
| Type       | G 20/6.30A/F               |
| GTIN (EAN) | 4008190086053              |
| Qty.       | 10 pc(s).                  |

**G 20/6.30A/F****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Technical data****Dimensions and weights**

|            |       |                 |            |
|------------|-------|-----------------|------------|
| Depth      | 5 mm  | Depth (inches)  | 0.197 inch |
| Height     | 20 mm | Height (inches) | 0.787 inch |
| Width      | 5 mm  | Width (inches)  | 0.197 inch |
| Net weight | 1.1 g |                 |            |

**Material data**

|        |            |
|--------|------------|
| Colour | Light Grey |
|--------|------------|

**System specifications**

|         |                  |
|---------|------------------|
| Version | Fuse accessories |
|---------|------------------|

**Fuse cartridges**

|                         |                     |                          |              |
|-------------------------|---------------------|--------------------------|--------------|
| Cartridge fuse          | G-Si. 5 x 20        | Characteristics          | quick-acting |
| Colour                  | Light Grey          | Current                  | 6.3 A        |
| Melting integral        | 32 A <sup>2</sup> s | Optical function display | No           |
| Power output (@ 1.5 In) | 2.6 W               | Rated breaking capacity  | 1.5 kA       |
| Version                 | Fuse accessories    | Voltage drop             | 130 mV       |

**Rating data**

|               |       |               |       |
|---------------|-------|---------------|-------|
| Rated voltage | 250 V | Rated current | 6.3 A |
|---------------|-------|---------------|-------|

**Classifications**

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC000035    | ETIM 7.0    | EC000035    |
| ETIM 8.0    | EC002704    | ETIM 9.0    | EC002704    |
| ECLASS 9.0  | 27-14-20-01 | ECLASS 9.1  | 27-14-20-01 |
| ECLASS 10.0 | 27-14-20-01 | ECLASS 11.0 | 27-14-20-01 |
| ECLASS 12.0 | 27-14-20-01 | ECLASS 13.0 | 27142001    |

**Approvals**

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

**Downloads**

|                    |   |
|--------------------|---|
| User Documentation | <a href="#">StorageConditionsTerminalBlocks</a> |
| Catalogues         | <a href="#">Catalogues in PDF-format</a>        |
| Brochures          |   |