

**AP VSSC6**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany  
[www.weidmueller.com](http://www.weidmueller.com)



End plates (AP) for the VSSC product series in light blue and black

**General ordering data**

Version	VSSC, End plate
Order No.	<a href="#">1063110000</a>
Type	AP VSSC6
GTIN (EAN)	4032248947553
Qty.	50 pc(s).

**AP VSSC6****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Technical data****Dimensions and weights**

Depth	81 mm	Depth (inches)	3.189 inch
Height	88.5 mm	Height (inches)	3.484 inch
Width	1.6 mm	Width (inches)	0.063 inch
Net weight	5.8 g		

**Temperatures**

Storage temperature	-40 °C...80 °C	Operating temperature	-40 °C...70 °C
Humidity	5...96 %		

**General data**

Colour	black	Design	miscellaneous
Protection degree	IP20	UL 94 flammability rating	V-0
Version	End plate		

**Classifications**

ETIM 6.0	EC000490	ETIM 7.0	EC000490
ETIM 8.0	EC000490	ETIM 9.0	EC000490
ECLASS 9.1	27-13-92-90	ECLASS 11.0	27-13-08-92
ECLASS 12.0	27-17-90-90	ECLASS 13.0	27179090

**Tender specification sheets**

Long specification	End plate for VSSC6	Short specification	End plate for VARITECTOR VSSC6
--------------------	---------------------	---------------------	--------------------------------

**Approvals**

Approvals

**GOSTEX**

ROHS Conform

**Downloads**

Engineering Data	<a href="#">CAD data – STEP</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>