

H6,0/15

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



For conductors from 0.25 to 6,0 mm² (AWG 24 - 10)
tin-plated copper
dimensional tolerances to DIN 46228 part 1
• supplied loose in polybag

General ordering data

Version	Wire-end ferrule, Standard, 15 mm, 15 mm, No
Order No.	0124700000
Type	H6,0/15
GTIN (EAN)	4008190003807
Qty.	500 pc(s).
Packaging	loose

Creation date February 5, 2024 4:15:19 PM CET

Catalogue status 27.01.2024 / We reserve the right to make technical changes.

H6,0/15**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data**Dimensions and weights**

Net weight 0.302 g

Technical data

Description of article	Wire end ferrule without plastic collar	Version	Standard
------------------------	---	---------	----------

Wire-end ferrules

Collar diameter (D2)	4.7 mm	Conductor cross-section	6 mm ²
Contact surface diameter (D1)	3.5 mm	Contact surface length (L2)	15 mm
L1 in mm	15 mm	Stripping length	15 mm
Wire connection cross section AWG, max.	AWG 10		

Classifications

ETIM 6.0	EC000005	ETIM 7.0	EC000005
ETIM 8.0	EC000005	ETIM 9.0	EC000005
ECLASS 9.0	27-40-02-01	ECLASS 9.1	27-40-02-01
ECLASS 10.0	27-40-02-01	ECLASS 11.0	27-40-02-01
ECLASS 12.0	27-40-02-01	ECLASS 13.0	27400201

Approvals

Approvals



ROHS Conform

UL File Number Search UL Website

Certificate no. (cULus) E499744

DownloadsEngineering Data [CAD data – STEP](#)Engineering Data [Zuken E3.S](#)Catalogues [Catalogues in PDF-format](#)

Brochures

Data sheet

H6,0/15

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

