


FIBOX
Enclosing innovations



Including : Base with screws for mounting plate/DIN-rail. cover with PUR gasket and quick-locking cover screws.



TRH 40	DIN-35 Mounting rail, for enclosures: (380 x 35 x 1)
TF 28037	Wall fastening lug (4 pcs), for enclosures:
TM 3640	Mounting plate, for enclosures:

Materials :		
Material :	ABS	
Base colour :	RAL_7035	
Cover colour :	RAL 7035 -light grey	
Gasket material :	Polyurethane	

Temperatures :		
Temperature °C (continuous) :	-40	... 60
Temperature °F (continuous) :	-40	... 140

(383 x 315 x 1)	
TH A	Grey plastic hinges (2 pcs)

Ratings :		
Ingress protection (EN 60529):	IP66; IP67;	
Impact Resistance (EN 62262):	IK07;	
electrical_insulation :	Totally insulated	
Halogen free (DIN/VDE 0472, Part 815) :	Yes	
UV resistance :	-	
Flammability Rating :	UL 94 HB	
Glow Wire Test (IEC 695-2-1) °C :	650C	

Certificates :		
SGSFimko_EURONORD		