

AB 081609

FIBOX
Enclosing innovations



Sample image

Order symbol : AB 081609

Product nr : 7083650

Description : Enclosure, ABS




Remarks : Grey cover

EAN : 6418074058805

El. number :

- Finland : 3435472
- Denmark : 8212003363
- Sweden : 7083650

Including : Base with screws for mounting plate/DIN-rail. cover with PUR gasket and stainless steel cover screws.



Dimensions :

	Height	Width	Depth
mm :	80	160	85
inch :	3.15	6.3	3.35

Materials :

Material :	ABS
Base colour :	RAL_7035
Cover colour :	RAL 7035 -light grey
Gasket material :	Polyurethane

Accessories :

TF 28037	Wall fastening lug (4 pcs), for enclosures:
TRH 1216	DIN-35 Mounting rail, for enclosures: (146 x 35 x 1)
TRM 0816	DIN-15 Mounting rail, for enclosures: (146 x 15 x 1)
TM 0816	Mounting plate, for enclosures: (71 x 134 x 1)
TH A	Grey plastic hinges (2 pcs)
TRM 0808	DIN-15 Mounting rail, for enclosures: (68 x 15 x 1)

Temperatures :

Temperature °C (continuous) :	-40 ... 60
Temperature °F (continuous) :	-40 ... 140

Ratings :

Ingress protection (EN 60529):	IP66; IP67;
Impact Resistance (EN 62262):	IK07;
electrical_insulation :	Totally insulated
Halogen free (DIN/VDE 0472, Part 815) :	Yes
UV resistance :	-
Flammability Rating :	UL 94 HB
Glow Wire Test (IEC 695-2-1) °C :	650C

Certificates :

SGSFimko_EURONORD