

AB 153412



Sample image

Order symbol : AB 153412

Product nr : 7083710

Description : Enclosure, ABS

Remarks : Grey cover

EAN : 6418074058874

El. number :

- Finland : 3435486
- Denmark : 8212003619
- Sweden : 7083710

Including : Base with screws for mounting plate/DIN-rail. cover with PUR gasket and stainless steel cover screws.

EURO153410-12

Dimensions :	Height	Width	Depth
mm :	150	340	120
inch :	5.91	13.39	4.72

Materials :

Material :	ABS
Base colour :	RAL_7035
Cover colour :	RAL 7035 -light grey
Gasket material :	Polyurethane

Temperatures :

Temperature °C (continuous) :	-40 ... 60
Temperature °F (continuous) :	-40 ... 140

Accessories :

TRH 34	DIN-35 Mounting rail, for enclosures: (307 x 35 x 1)
TF 28037	Wall fastening lug (4 pcs), for enclosures:
TRH 15	DIN-35 Mounting rail, for enclosures: (122 x 35 x 1)
TM 1534	Mounting plate, for enclosures: (303 x 136 x 1)
TH A	Grey plastic hinges (2 pcs)

Ratings :

Ingress protection (EN 60529):	IP66; IP67;
Impact Resistance (EN 62262):	IK07;
electrical_insulation :	Totally insulated
Halogen free (DIN/VDE 0472, Part 815) :	Yes
UV resistance :	-
Flammability Rating :	UL 94 HB
Glow Wire Test (IEC 695-2-1) °C :	650C

Certificates :

SGSFimko_EURONORD