

ALN 123608



Sample image

Order symbol : ALN 123608

EAN : 6418074011404

Product nr : 7811250

El. number :

UL Name : ALN UL 123608

- Finland : 3420050
- Denmark : 8212004728
- Sweden : 2500914

Description : Enclosure, aluminium

Including : Base with screws for mounting plate/DIN-rail. cover with PUR gasket and stainless steel cover screws.

| Dimensions : | Height | Width | Depth |
|---------------------|---------------|--------------|--------------|
| mm : | 125 | 362 | 81 |
| inch : | 4.92 | 14.25 | 3.19 |

Materials :

| | |
|-------------------|--------------|
| Material : | Aluminum |
| Base colour : | RAL_7001 |
| Cover colour : | RAL 7001 |
| Gasket material : | Polyurethane |

Temperatures :

| | |
|-------------------------------|-------------|
| Temperature °C (continuous) : | -50 ... 80 |
| Temperature °F (continuous) : | -60 ... 175 |

Accessories :

| | |
|-----------|--|
| AM 1212 | Mounting plate, for enclosures: (107 x 110 x 1) |
| MR 75005 | Selftapping taptite screw M5, for enclosures: |
| MRS 28541 | Wall fastening lug (2 pcs), for enclosures: (15 x 50 x 1) |
| ARH 12 | DIN-35 Mounting rail, for enclosures: (105 x 35 x 1) |
| AM 1236 | Mounting plate, for enclosures: (107 x 347 x 1) |
| AM 1222 | Mounting plate, for enclosures: (107 x 207 x 1) |
| ARH 36 | DIN-35 Mounting rail, for enclosures: (343 x 35 x 1) |

Ratings :

| | |
|---|----------------------|
| Ingress protection (EN 60529): | IP66; IP67; IP68; |
| Impact Resistance (EN 62262): | IK08; |
| electrical_insulation : | Not insulated |
| Halogen free (DIN/VDE 0472, Part 815) : | Yes |
| UV resistance : | UL 746C |
| UL Type | NEMA__1_4_4X_6_12_13 |

Certificates :

SGSFIMKO_ALU

