

inch : 6.38 6.42 3.58

Materials :

Material : Aluminum
Base colour : RAL_7001
Cover colour : RAL 7001
Gasket material : Polyurethane

Temperatures :

Temperature °C (continuous) : -50 ... 80
Temperature °F (continuous) : -60 ... 175

(140 x 35 x 1)

ARM 0615 DIN-15 Mounting rail, for enclosures:
(140 x 15 x 1)
AM 1616 Mounting plate, for enclosures:
(146 x 146 x 1)
MR 75005 Selftapping taptite screw M5, for enclosures:
MRS 28541 Wall fastening lug (2 pcs), for enclosures:
(15 x 50 x 1)

Ratings :

Ingress protection (EN 60529): IP66; IP67;
Impact Resistance (EN 62262): IK08;
electrical_insulation : Not insulated
Halogen free (DIN/VDE 0472, Part 815) : Yes
UV resistance : UL 746C
UL Type NEMA__1_4_4X_6_12_13

Certificates :

SGSFIMKO_ALU