

ALN 232011



Sample image

Order symbol : ALN 232011

Product nr : 7811350

UL Name : ALN UL 232011

Description : Enclosure, aluminium

Remarks : Aluminium

EAN : 6418074016164

El. number :

- Finland : 3420035
- Denmark : 8212045758
- Sweden : 2500921

Including : Base with screws for mounting plate/DIN-rail. cover with PUR gasket and stainless steel cover screws.

ALN232011-18combi

Dimensions :	Height	Width	Depth
mm :	230	200	110
inch :	9.06	7.87	4.33

Materials :

Material :	Aluminum
Base colour :	RAL_7001
Cover colour :	RAL 7001
Gasket material :	Polyurethane

Temperatures :

Temperature °C (continuous) :	-50 ... 80
Temperature °F (continuous) :	-60 ... 175

Accessories :

ARH 2320	DIN-35 Mounting rail, for enclosures: (180 x 35 x 1)
MRS 28541	Wall fastening lug (2 pcs), for enclosures: (15 x 50 x 1)
AM 2320	Mounting plate, for enclosures: (215 x 184 x 1)

Ratings :

Ingress protection (EN 60529):	IP66; IP67; IP68;
Impact Resistance (EN 62262):	IK08;
electrical_insulation :	Not insulated
Halogen free (DIN/VDE 0472, Part 815) :	Yes
UV resistance :	UL 746C
UL Type	NEMA__1_4_4X_6_12_13

Certificates :

SGSFIMKO_ALU