

ALN 316018



Sample image

Order symbol : ALN 316018

Product nr : 7811480

Description : Enclosure, aluminium

Remarks : Aluminium

EAN : 6418074016263

El. number :

- Finland : 3420008
- Denmark : 8212045868

Including : Base with screws for mounting plate/DIN-rail. cover with PUR gasket and stainless steel cover screws.

7811480_ALN316018

Dimensions :	Height	Width	Depth
mm :	310	600	180
inch :	12.2	23.62	

Accessories :

AM 3160 Mounting plate, for enclosures:
(293 x 585 x 1)

Materials :

Material : Aluminum
Base colour : RAL_7001
Cover colour : RAL 7001
Gasket material : Polyurethane

Ratings :

Ingress protection (EN 60529): IP66; IP67; IP68;
Impact Resistance (EN 62262): IK08;
electrical_insulation : Not insulated
Halogen free (DIN/VDE 0472, Part 815) : Yes
UV resistance : UL 746C
UL Type NEMA__1_4_4X_6_12_13

Temperatures :

Temperature °C (continuous) : -40 ... 80
Temperature °F (continuous) : -60 ... 175