

ARCA 302015W No MP



Sample image

Order symbol : ARCA 302015W No MP

Product nr : 8120122N

UL Code : UL508A

Description : Cabinet, PC

Remarks : Grey cover with window, 1-point locking, hinges on the long side

EAN : 6418074093981

El. number :

- Denmark : 8212054040

Including : Cabinet base. door with PUR gasket. 3mm double bit lock(s) with key. S versions with swinghandle 2-point locking system. Door guide included.

Dimensions :	Height	Width	Depth
mm :	300	200	150
inch :	7.87	11.81	5.91

Materials :

Material :	Polycarbonate
Base colour :	RAL_7035
Cover colour :	Clear transparent
Gasket material :	Polyurethane

Temperatures :

Temperature °C (continuous) :	-40 ... 80
Temperature °F (continuous) :	-40 ... 175

Accessories :

MPP ARCA 3020	Mounting plate perforated (250x150x2 mm - 26x11 mm) (250 x 150 x 2)
DRS ARCA 302015	DIN rail frame set (285 x 185 x 35)
MPMP ARCA 3020	Mounting plate multiperforated (250x150x2 mm - ø3.6 mm)
PMK ARCA 20	PoleMounting kit, for pole ø100-300mm (385 x 285 x 35)
RCS ARCA 3020	Rain canopy set for size 3020
MPS ARCA 3020	Mounting plate (250x150x2 mm) (250 x 150 x 2)
IDS ARCA 3020	Inner door set (285 x 185 x 35)
MPX ARCA 3020	Mounting plate (250x150 mm) (250 x 150 x 15)

Ratings :

Ingress protection (EN 60529):	IP65;
Impact Resistance (EN 62262):	IK08;
electrical_insulation :	Totally insulated
Halogen free (DIN/VDE 0472, Part 815) :	Yes
UV resistance :	UL 746C

Flammability Rating :

UL 94 5VA

Glow Wire Test (IEC 695-2-1) °C :

960C