

ARCA 507030 No MP



Sample image

Order symbol : ARCA 507030 No MP

Product nr : 8120031N

UL Code : UL508A

Description : Cabinet, PC

Remarks : Grey cover, 2-point locking, hinges on the short side

EAN : 6418074089458

El. number :

- Finland : 3424575
- Denmark : 8212097544

Including : Cabinet base. door with PUR gasket. 3mm double bit lock(s) with key. S versions with swinghandle 2-point locking system. Door guide included.

Dimensions :	Height	Width	Depth
mm :	500	700	300
inch :	19.69	27.56	11.81

Materials :

Material :	Polycarbonate
Base colour :	RAL_7035
Cover colour :	RAL 7035 -light grey
Gasket material :	Polyurethane

Temperatures :

Temperature °C (continuous) :	-40 ... 80
Temperature °F (continuous) :	-40 ... 175

Accessories :

MPX ARCA 7050	Mounting plate (630x430 mm) (630 x 430 x 15)
PMK ARCA 70	PoleMounting kit, for pole ø100-300mm (685 x 485 x 35)
RCS ARCA 5070	Rain canopy set for size 5070
DSP ARCA RM	Door stopper ARCA, right, midsize 5070-8060
DRS ARCA 507030	DIN rail frame set (685 x 485 x 35)
IDS ARCA 5070	Inner door set
DSP ARCA LM	Door stopper ARCA, left, midsize 5070-8060
MPS ARCA 7050	Mounting plate (630x430x2 mm) (630 x 430 x 2)
MPMP ARCA 7050	Mounting plate multiperforated (630x430x2 mm - ø3.6 mm)
MPP ARCA 5070	Mounting plate perforated (630x430x2 mm - 26x11 mm)

Ratings :

Ingress protection (EN 60529):	IP66;
Impact Resistance (EN 62262):	IK10;
electrical_insulation :	Totally insulated

Halogen free (DIN/VDE 0472, Part 815) :	Yes
UV resistance :	UL 746C
Flammability Rating :	UL 94 5VA
Glow Wire Test (IEC 695-2-1) °C :	960C
UL Type	NEMA__1_4_4X_12_13