

ARCA 608030 No MP



Sample image

Order symbol : ARCA 608030 No MP

Product nr : 8120029N

UL Code : UL508A

Description : Cabinet, PC

Remarks : Grey cover, 2-point locking, hinges on the short side

EAN : 6418074089465

El. number :

- Finland : 3424581
- Denmark : 8212097531

Including : Cabinet base. door with PUR gasket. 3mm double bit lock(s) with key. S versions with swinghandle 2-point locking system. Door guide included.

Dimensions :	Height	Width	Depth
mm :	600	800	300
inch :	31.5	23.62	12.2

Materials :

Material :	Polycarbonate
Base colour :	RAL_7035
Cover colour :	RAL 7035 -light grey
Gasket material :	Polyurethane

Temperatures :

Temperature °C (continuous) :	-40 ... 80
Temperature °F (continuous) :	-40 ... 175

Accessories :

DRS ARCA 608030	DIN rail frame set (785 x 585 x 35)
RCS ARCA 6080	Rain canopy set for size 6080
DSP ARCA RM	Door stopper ARCA, right, midsize 5070-8060
MPS ARCA 8060	Mounting plate (730x530x2 mm)
DSP ARCA LM	Door stopper ARCA, left, midsize 5070-8060
IDS ARCA 6080	Inner door set
MPMP ARCA 8060	Mounting plate multiperforated (730x530x2 mm - ø3.6 mm)
PMK ARCA 80	PoleMounting kit, for pole ø100-300mm (785 x 585 x 35)
MPP ARCA 6080	Mounting plate perforated (730x530x2 mm - 26x11 mm)
MPX ARCA 8060	Mounting plate (730x530 mm) (730 x 530 x 15)

Ratings :

Ingress protection (EN 60529):	IP66;
Impact Resistance (EN 62262):	IK10;
electrical_insulation :	Totally insulated

Halogen free (DIN/VDE 0472, Part 815) :	Yes
UV resistance :	UL 746C
Flammability Rating :	UL 94 5VA
Glow Wire Test (IEC 695-2-1) °C :	960C
UL Type	NEMA__1_4_4X_12_13