

ARCA 705030W No MP



Sample image

Order symbol : ARCA 705030W No MP

Product nr : 8120137N

UL Code : UL508A

Description : Cabinet, PC


Remarks : Grey cover with window, 2-point locking, hinges on the long side

EAN : 6418074094032

El. number :

- Denmark : 8212054244

Including : Cabinet base. door with PUR gasket. 3mm double bit lock(s) with key. S versions with swinghandle 2-point locking system. Door guide included.



Dimensions :

	Height	Width	Depth
mm :	700	500	300
inch :	19.69	27.56	12.2

Materials :

Material :	Polycarbonate
Base colour :	RAL_7035
Cover colour :	Clear transparent
Gasket material :	Polyurethane

Temperatures :

Temperature °C (continuous) :	-40 ... 80
Temperature °F (continuous) :	-40 ... 175

Accessories :

MPX ARCA 7050	Mounting plate (630x430 mm) (630 x 430 x 15)
IDS ARCA 7050	Inner door set (685 x 485 x 35)
DSP ARCA RM	Door stopper ARCA, right, midsize 5070-8060
RCS ARCA 7050	Rain canopy set for size 7050
MPP ARCA 7050	Mounting plate perforated (630x430x2 mm - 26x11 mm)
DSP ARCA LM	Door stopper ARCA, left, midsize 5070-8060
DRS ARCA 705030	DIN rail frame set (685 x 485 x 35)
MPS ARCA 7050	Mounting plate (630x430x2 mm) (630 x 430 x 2)
MPMP ARCA 7050	Mounting plate multiperforated (630x430x2 mm - $\varnothing 3.6$ mm)
PMK ARCA 50	PoleMounting kit, for pole $\varnothing 100-300$ mm (485 x 385 x 35)

Ratings :

Ingress protection (EN 60529):	IP65;
Impact Resistance (EN 62262):	IK08;
electrical_insulation :	Totally insulated
Halogen free (DIN/VDE 0472, Part 815) :	Yes

UV resistance :	UL 746C
Flammability Rating :	UL 94 5VA
Glow Wire Test (IEC 695-2-1) °C :	960C

Certificates :

Certificate FI 40467