

## Product data sheet

# 610 184 3

## Ferrule crimping tool PEW 8.184

Sideways insertion

- Self-adjusting adaptation to the required size of wire-end ferrule
- Wire-end ferrules are inserted sideways into the tool
- Force magnified by lever action to ensure fatigue-free working
- Precise, factory-set (calibrated) crimping pressure
- Consistent crimping quality with forced-lock completion of crimping process (can be released)
- Black-oxide finish
- Specially hardened spring steel
- Ergonomic 2-component grips



### General

Item number	610 184 3
EAN	4049002104244
Weight	410 g
Dimension	180 mm
Dimension packaging	250 x 108 x 43 mm

### Specifications

Finish	black-oxide finish
Grips	2-component grips
Range of applications	Ferrules
Capacity	0.08 – 10.0 mm <sup>2</sup> / AWG 28 – 8
Twin wire-end ferrules	2x 0.25 – 6.0 mm <sup>2</sup> / 2x AWG 22 – 8

### Classification

eCl@ss 10.1	ACD215012
ETIM 7.0	EC000168
proficl@ss 7.0	AAA946c003

*With reservations regarding technical modifications and errors. Illustration may vary.*