



Part Number:	SM150906-1	
DESCRIPTION:	Dynamic Speaker	
DRAWN	CJ	8/26/2016
CHECKED	P.D.	8/26/2016
APPROVED	J.S.	8/26/2016

This document contains data proprietary to DB Unlimited. Any use or reproduction, in any form, without prior written permission of DB Unlimited is prohibited. All terms and conditions can be found at www.dbunlimitedco.com


Top View




Side View (1)




Bottom View



Pad Layout



Side View (2)



Items	Specifications	Conditions
Sound Pressure Level	90.5	dB (@ 10cm), Avg.
Resonant Frequency	900	Hz
Frequency Range	900 ~ 10,000	Hz
Nominal Power	0.67	W
Max. Power	1	W
Impedance	6.5	Ω
Cone Material	Mylar	
Mount Type	Flush Mount	
Storage Temperature	-40 ~ +85	°C
Operating Temperature	-30 ~ +70	°C
Weight	0.8	g

REVISION HISTORY

REV	DESCRIPTION	DATE	APPROVED
	Released from Engineering	8/26/2016	J.S.
1	Add polarity marking, update SPL condition	9/22/2017	C.E.

NOTES

- 1) All dimensions are in mm unless otherwise noted
- 2) All tolerances are ± 0.5 mm unless otherwise noted
- 3) All parts meet RoHS
- 4) Subject to change or redrawn without notice