




REV.	ECN NO.	DATE	SIGN	DESCRIPTION
C	C200639	2020/05/11	Victor Hung	△ X2
D	C220464	2022/04/07	Ruru	△ X4
E	C230087	2023/01/31	Vicky	△ XI



UNIT: mm	TOLERANCE	TITLE	ITEM NO	DATE
±0.5 mm		XLOK, C-20A, CABLE W/O SR F, M, FI SCREW IN, PUSH LOCK		2020/05/11
		SCALE 8:5 SIZE A4 SHEET 1 OF 2	CC-XXBFMB-QL8XPP	2020/05/11
		REV. E MC-REV. A.3 (C): Inspection item	ALLTW	2020/05/11

**Amphenol LTW**  
安費諾亮泰企業股份有限公司

DRAWN BY: Victor Hung  
CHECKED BY: Aric Ko  
APPROVED BY: Max Yang

DATE: 2020/05/11  
DATE: 2020/05/11  
DATE: 2020/05/11

△ XX: No. Of Pin  
CC-XXBFMB-QL8XPP

Note: △ B △ D  
 \* RoHS Compliant  
 \* (C) Important dimension  
 \* Waterproof rate: IP68, mated 1m/24h Connector  
 Housing: Thermoplastic, Black  
 Pin: Copper Alloy, Silver Plated  
 Nut: Thermoplastic, Black  
 O-Ring-1: Rubber, Gray  
 O-Ring-2: Rubber, Dark Gray  
 \* Clamp Ring: Thermoplastic, Black  
 \* Sealing Nut: Thermoplastic, Black  
 \* Seals: Rubber

S: With Red Color Seal 1, Cable OD 6.0~8.0mm.  
 M: With Yellow Color Seal 2, Cable OD 8.0~10.0mm.  
 L: With Blue Color Seal 3, Cable OD 10.0~12.0mm.  
 A: With Seal 1 & Seal 2 & Seal 3.

