

Materials :

Material :	ABS
Base colour :	RAL_7035
Cover colour :	RAL 7035 -light grey
Gasket material :	Polyurethane

NEO MPS 4232	Metal mounting plate (375 x 265 x 1)
PMK NEO 30	Polemounting kit (400 x 300 x 30)
WMK NEO plastic	Wall mounting kit plastic (80 x 70 x 40)
DRS NEO 423215	DIN rail frame set

Temperatures :

Temperature °C (continuous) :	-40 ... 60
Temperature °F (continuous) :	-40 ... 140

Ratings :

Ingress protection (EN 60529):	IP66; IP67;
Impact Resistance (EN 62262):	IK08;
electrical_insulation :	Totally insulated
Halogen free (DIN/VDE 0472, Part 815) :	Yes
UV resistance :	-
Flammability Rating :	UL 94 HB
Glow Wire Test (IEC 695-2-1) °C :	650C

Certificates :

Certificate FI 40693 A1.pdf