

Dimensions :

	Height	Width	Depth
mm :	560	280	130
inch :	22.05	11.02	5.12

Materials :

Material :	Polycarbonate
Base colour :	RAL_7035
Cover colour :	RAL 7035 -light grey
Gasket material :	Polyurethane

Temperatures :

Temperature °C (continuous) :	-40 ... 80
Temperature °F (continuous) :	-40 ... 175

Accessories :

EKTZR	Extension frame, for enclosures: (560 x 280 x 50)
EKTVT	Mounting plate, for enclosures: (518 x 238 x 1)
EKV 22	DIN-35 Mounting rail, for enclosures: (235 x 35 x 1)
EKV 50	DIN-35 Mounting rail, for enclosures: (515 x 35 x 1)

Ratings :

Ingress protection (EN 60529):	IP65;
Impact Resistance (EN 62262):	IK08;
electrical_insulation :	Totally insulated
Halogen free (DIN/VDE 0472, Part 815) :	Yes
UV resistance :	UL 746C
Flammability Rating :	UL 94 V0
Glow Wire Test (IEC 695-2-1) °C :	960C

Certificates :

DSS_FI_41597_A1