



**Part Number :** 731000157

**Product Description :** 75 Ohms, SMB PCB Jack Receptacle, Vertical

**Series Number :** 73404

**Status :** Active

**Product Category :** RF / Coaxial Connectors



---

## Documents & Resources

### Drawings

[Drawing 731000157\\_sd.pdf](#)

### 3D Models and Design Files

[3D Model 731000157\\_stp.zip](#)


### Specifications

[Product Specification PS-73598-0093-001.pdf](#)

---

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead per D(2023)3788-DC (14 Jun 2023)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

### Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

### Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration

- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

---

## Part Details

### General

Status	Active
Category	RF / Coaxial Connectors
Series	73404
Description	75 Ohms, SMB PCB Jack Receptacle, Vertical
Product Family	SMB RF Connectors
Product Name	SMB
Style	PCB
Type	Subminiature
UPC	800753686496

### Electrical

Frequency	4 GHz
Impedance	75Ω
Power / Voltage	VOLTAGE: 335 Vrms@Sea Level

### Physical

Gender	Jack
Keying to Mating Part	None
Net Weight	0.605/g
Orientation	Straight
Packaging Type	Tray
Panel Mount	No
Panel Mount Method	N/A
PCB Mounting	Through Hole
PCB Thickness - Recommended	3.20mm
Reverse Polar	No
Wire/Cable Type	N/A

## Solder Process Data

Max-Duration	10
Lead-Free Process Capability	SMC&WAVE
Max-Cycle	2
Max-Temp	260

---

This document was generated on Feb 26, 2024