



AMP

TE Internal #: 91388-1
 Hand Crimping Tools, Commercial Crimp Tooling, Operator
 Releasable & Adjustable, Removable/Interchangeable, TE Product
 Specification (114-)

[View on TE.com >](#)

Application Tooling > Hand Crimping Tools



Tool Grade: **Commercial Crimp Tooling**
 Ratchet Configuration: **Operator Releasable & Adjustable**
 Die Sets Type: **Removable/Interchangeable**
 Specification Type: **TE Product Specification (114-)**
 TE Certification: **Upon Request for Fee**

Features

Other

Crimp Form-Wire Barrel Type	Open Barrel - F Crimp
Tool Grade	Commercial Crimp Tooling
Ratchet Configuration	Operator Releasable & Adjustable
Die Sets Type	Removable/Interchangeable
Specification Type	TE Product Specification (114-)
TE Certification	Upon Request for Fee
Power Technology Type	Battery, Electric, Manual
Tooling Type	PRO-CRIMPER Hand Tool

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Out of Scope
EU ELV Directive 2000/53/EC	Out of Scope
China RoHS 2 Directive MIIT Order No 32, 2016	Not reviewed for China RoHS compliance
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC



Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
-----------------	---

Solder Process Capability	Not applicable for solder process capability
---------------------------	--

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 <p>TE Part # 1586314-1 VAL-U-LOK PIN BR TN 22-18 LP</p>	 <p>TE Part # 1586314-2 VAL-U-LOK PIN BR AU 22-18 LP</p>	 <p>TE Part # 1586314-3 VAL-U-LOK PIN PHBZ SN 24-18 LP</p>	 <p>TE Part # 1586315-1 VAL-U-LOK SKT BR SN 24-18 LP</p>
 <p>TE Part # 1586315-2 VAL-U-LOK SKT BR AU 24-18 LP</p>	 <p>TE Part # 1586315-3 VAL-U-LOK SKT PHBZ SN 24-18 LP</p>	 <p>TE Part # 1586315-4 VAL-U-LOK SKT PHBZ AU 24-18 LP</p>	 <p>TE Part # 1586314-4 VAL-U-LOK PIN PHBZ AU 24-18 LP</p>
 <p>TE Part # 3-1586040-6 6P VAL-U-LOK VRT HDR W/P V0 gold</p>	 <p>TE Part # 3-1586040-8 8P VAL-U-LOK VRT HDR W/P V0 gold</p>	 <p>TE Part # 4-1586040-6 16P VAL-U-LOK VRT HDR W/P V0 gold</p>	


Customers Also Bought




TE Part #1-968879-1
Timer Connector Housing




TE Part #539660-1
ADERENDHUELSEN (Ferrule) Crimp
Tool




TE Part #215297-7
7P HV100 REC CON. TE, 7.0MM



TE Part #2029111-3
3P PLUG SR VAL-U-LOK FH GW



TE Part #794954-4
4P RCPT VAL-U-LOK V2



TE Part #1586315-2
VAL-U-LOK SKT BR AU 24-18 LP



TE Part #2822356-1
070 TYPE NEW RUBBER PLUG S



TE Part #2238020-1
VAL-U-LOK PIN BR TN 22-18 LP



TE Part #1586343-1
VAL-U-LOK EXTRACTION TOOL

Documents

Datasheets & Catalog Pages

[1-1773865-2_1015_Commercial Manual Hand Tools](#)

English

Bottoming Dies

English

Instruction Sheets

[Instruction Sheet \(U.S.\)](#)

English