

General ordering data	
Order No.	1579010000
Part designation	WQB B/2
Version	Cross-connector / link for modular terminal, Cross-connector, No. of poles: 2
EAN	4008190021696
Qty.	50 pc(s).

Additional technical data	
Explosion-tested version "Ex e"	No
Installation advise	Direct m

Installation advice Direct mounting

Height	12 mm
No. of cross-connected terminals	2
Pitch	5.1 mm
Rated current, multi-pole	24 A
Rated voltage	0 V
Type	Cross-connector
Type of fixing	Screwed
Function	Cross-connector
No. of poles	2
Doting data	

Rating data	
Rated voltage	0 V

Approvais	
Approvals institutes	n a

Classifications eClass 4.1 27-14-11-99 eClass 5.0 27-14-11-40		
	27 14 11 00	
COIDSS 3.0 21-14-11-40	 	
eClass 5.1 27-14-11-40		

Similar products

1579020000	WQB B/3	Cross-connector / link for modular terminal, Cross-connector, No. of poles: 3
1579030000	WQB B/4	Cross-connector / link for modular terminal, Cross-connector, No. of poles: 4
1579040000	WQB B/6	Cross-connector / link for modular terminal, Cross-connector, No. of poles: 6
1579050000	WQB B/10	Cross-connector / link for modular terminal, Cross-connector, No. of poles: 10
1579060000	WQB B/24	Cross-connector / link for modular terminal, Cross-connector, No. of poles: 24