


D Shapes		Part Number
H	W	
0.040	0.150	2531-1011-1018
0.040	0.200	2531-1011-1019
0.060	0.125	2531-1011-1020
0.060	0.150	2531-1011-0122
0.060	0.250	2531-1011-0229
0.070	0.180	2531-1011-0214
0.090	0.090	2531-1011-0123
0.090	0.150	2531-1011-0150
0.100	0.300	2531-1011-0224
0.120	0.150	2531-1011-0124
0.125	0.090	2531-1011-0151
0.125	0.250	2531-1011-0125
0.125	0.187	2531-1011-1021
0.140	0.250	2531-1011-0126
0.140	0.375	2531-1011-0163
0.150	0.150	2531-1011-0152
0.157	0.315	2531-1011-0220
0.158	0.433	2531-1011-0186
0.196	0.315	2531-1011-0153
0.200	0.190	2531-1011-0154
0.250	0.250	2531-1011-0127
0.250	0.375	2531-1011-0128
0.375	0.500	2531-1011-0155
0.500	0.500	2531-1011-0226
0.562	0.709	2531-1011-1022

REV	DESCRIPTION	DATE	APPR. BY
-	Initial Release	10/27/23	K. COSTA



MASTER COPY
WHEN INK IS RED
TEPN: 2531
ACCEPTED BY: KC
DATE: 12/1/23

NOTES:
NOTE 1: POLYURETHANE FOAM CORE.
NOTE 2: NICKEL PLATING OVER COPPER SUBSTRATE FABRIC.
NOTE 3: 3M ADHESIVE TRANSFER TAPE 467MP OR EQUIVALENT.
NOTE 4: FLAMMABILITY RATING UL 94 V-0 RATED.
NOTE 5: COMPRESSION PERMANENT DEFORMATION ASTM D395 ≤20%.
NOTE 6: SURFACE RESISTANCE ASTM F390 ≤0.07 OHMS/INCH2.
NOTE 7: WORKING TEMPERATURE WITHOUT PSA: -40C - 120C.
NOTE 8: WORKING TEMPERATURE WITH PSA: -40C - 90C.
NOTE 9: UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES.
NOTE 10: CONSULT MANUFACTURER FOR AVAILABLE LENGTHS.

FOR ITEM:
MAT'L: SEE NOTES

UNLESS OTHERWISE SPECIFIED
ALL TOLERANCES TO BE:
≤0.787 ± 0.011
0.787-1.969 ± 0.019
1.969-3.937 ± 0.027
3.937-19.685 ± 0.038
19.685-39.369 ± 0.118
>39.369 ± 0.315

TECH ETCH		TECH-ETCH, INC. 45 Aldrin Road Plymouth MA 02360	
		FILE: 2531	TOOL NO.: N/A
DATE: 10/27/23		DRAWN BY: K. Costa	APPR. BY: K. Costa
CAT. NO.: 2531-1011-XXXX-XX.XX		SHEET: 1 OF 1	SIZE:
PART NAME Metalized Fabric Gasket		SCALE: 1:1	