




DESIGNED & DIMENSIONED IN MILLIMETERS [ENGLISH]



DETAIL 'A'
SCALE 4 : 1



-30 POSITION SHOWN

TABLE 1

POSITION	"A"	"B"
-005	3.200 [.1260]	10.00 [.394]
-010	7.200 [.2835]	14.00 [.551]
-013	9.600 [.3780]	16.40 [.646]
-020	15.200 [.5984]	22.00 [.866]
-023	17.600 [.6929]	24.40 [.961]
-025	19.200 [.7559]	26.00 [1.024]
-030	23.200 [.9134]	30.00 [1.181]
-040	31.200 [1.2283]	38.00 [1.496]
-049	38.400 [1.5118]	45.20 [1.780]
-050	39.200 [1.5433]	46.00 [1.811]
-060	47.200 [1.8583]	54.00 [2.126]
-070	55.200 [2.1732]	62.00 [2.441]
-075	59.200 [2.3307]	66.00 [2.598]

DESIGNED & DIMENSIONED IN MILLIMETERS [ENGLISH]


DETAIL 'A'
SCALE 4 : 1

TABLE 3		
OPTION	"C"	
NONE, -L, -SL, OR -DS	3.30	[0.130]
* -EGPS	2.50	[0.098]

(* = NOT RELEASED FOR PRODUCTION)

NOTES:
 1. \odot REPRESENTS A CRITICAL DIMENSION.
 2. MIRROR IMAGE FOOTPRINT ON OTHER SIDE OF PCB.
 3. STENCIL TO BE 0.150 [0.006] THICK.

POSITION	"A"	"B"
-005	3.200 [1.126]	10.00 [0.394]
-010	7.200 [2.835]	14.00 [0.551]
-013	9.600 [3.780]	16.40 [0.646]
-020	15.200 [5.984]	22.00 [0.866]
-023	17.600 [6.929]	24.40 [0.961]
-025	19.200 [7.559]	26.00 [1.024]
-030	23.200 [9.134]	30.00 [1.181]
-040	31.200 [1.2283]	38.00 [1.496]
-049	38.400 [1.5118]	45.20 [1.780]
-050	39.200 [1.5433]	46.00 [1.811]
-060	47.200 [1.8583]	54.00 [2.126]
-070	55.200 [2.1732]	62.00 [2.441]
-075	59.200 [2.3307]	66.00 [2.598]

UNLESS OTHERWISE SPECIFIED,
 DIMENSIONS ARE IN MILLIMETERS.
 TOLERANCES ARE:
 DECIMALS
 XX: ± 0.01
 XXX: ± 0.004
 XXXX: ± 0.0020

PROPRIETARY NOTE
 THIS DOCUMENT CONTAINS INFORMATION
 CONFIDENTIAL AND PROPRIETARY TO
 SAMTEC, INC. AND SHALL NOT BE REPRODUCED
 OR TRANSFERRED TO OTHER DOCUMENTS OR
 DISCLOSED TO OTHERS OR USED FOR ANY
 PURPOSE OTHER THAN THAT WHICH IT WAS
 OBTAINED WITHOUT THE EXPRESSED WRITTEN
 CONSENT OF SAMTEC, INC.