


# SHROUDED **HEADER & STACKER**



(2.00 mm) .0787" PITCH • LTMM/ZLTMM SERIES

### LTMM/ZLTMM

Mates:

SQT, SQW, ESQT, SMM

#### **SPECIFICATIONS**

Insulator Material: Black Liquid Crystal Polymer
Terminal Material: Phosphor Bronze
Plating:
Sn or Au over
50 μ" (1.27 μm) Ni
Operating Temp Range:
-55 °C to +105 °C with Tin;
-55 °C to +125 °C with Gold

#### **PROCESSING**

Lead-Free Solderable: SMT Lead Coplanarity: (0.10 mm) .004 max

LTMM



04, 05,

06, 07,

08, 10, 12,

13, 15, 17,

20, 22, 25

(Standard sizes)

02

**PLATING OPTION** 

-F = Gold flash on post, Matte Tin on tail

= 10 µ" (0.25 µm) Gold on post, Matte Tin on tail

-T = Matte Tin

## OPTION

Leave blank for Through-hole

-RA = Right-angle

-SM = Surface Mount

## **OPTION**


-"XX" = Polarized Position


-LC Locking Clip (-SM only) (Manual placement required)

**-K** = (7.50 mm) .295" DIA Film Pick & Place Pad (-SM only)

-TR = Tape & Reel (-SM only)

**-FR** = Full Reel Tape & Reel (must order max. quantity per reel; contact Samtec for quantity breaks) (-SM only)











## ALSO AVAILABLE MOQ Required

Other sizes Other plating

# ZLTMM

04, 05,

06, 07,

Specify LEAD

STYLE

from chart

## PLATING OPTION






-"XXX" -"XX" = Body = Polarized Height Position

= 10 µ" (0.25 µm) Gold on post, Matte Tin on tail

-F = Gold flash

on post, Matte Tin on tail

-T = Matte Tin




STYLE	(OAL)	HEIGHT
<b>-</b> 75	(9.58) 0.377	(7.42) 0.292
-62	(10.08) 0.397	(7.92) 0.312
-65	(10.49) 0.413	(8.33) 0.328
-73	(12.09) 0.476	(9.93) 0.391
-63	(14.10) 0.555	(11.94) 0.470
-66	(15.09) 0.594	(12.93) 0.509
-69	(15.60) 0.614	(13.44) 0.529
-74	(17.09) 0.673	(14.94) 0.588
-70	(17.60) 0.693	(15.44) 0.608
<b>-71</b>	(21.08) 0.830	(18.92) 0.745
-72	(21.62) 0.851	(19.46) 0.766

#### Note:

For added mechanical stability, Samtec recommends mechanical board spacers be used in applications with gold or selective gold plated connectors. Contact ipg@samtec.com for more information.

## 08, 10, 12, 13, 15, 17, 20, 22, 25 (Standard sizes) No. of positions + (2.39) .094 回 回



This Series is non-standard, non-returnable.