



NYB35-40006

Industrial Box PC with Intel® Core™ i5-7300U, 16 GB DDR4 RAM (non-ECC), No storage, No OS, no PCIe slot, NYML port

Specifications

Max. number of motion axes	0 axes
Processor family	Intel® Core™ i5
Processor specification	7300U (2.6 GHz)
Cooling method	Passive cooling (fanless)
Memory	16 GB RAM (non ECC)
Storage	No Storage
Operating system	No OS
Expansion slot	No Expansion
Modular port	NYML
Communication port(s)	EtherNet/IP, Ethernet TCP/IP, USB
Video output	DVI-I
Material housing	Aluminium, black
Degree of protection (IP)	IP20
Operating temperature	0-55 °C
Supply voltage DC	20.4-28.8 V
Product Height (unpacked)	41 mm
Product Width (unpacked)	282 mm
Product Depth (unpacked)	195 mm
Product Weight (unpacked)	1900 g

Accessories



FH-VUAB 2M

Vision system accessory FH USB cable touch panel 2 m



FH-VUAB 5M

Vision system accessory FH USB cable touch panel 5 m

NY000-AT00

CFast MLC, Capacity: 64 GB

NY000-AT01

CFast MLC, Capacity: 128 GB

NY000-AT02

CFast MLC, Capacity: 256 GB



NYM12W-C1000

Industrial Monitor, 12.1" display with capacitive touchscreen, Build-in mounting, DVI-D port



NYM12W-C1060

Industrial Monitor, 12.1" display with capacitive touchscreen, Build-in mounting, NYML port



NYM15W-C1000

Industrial Monitor, 15.4" display with capacitive touchscreen, Build-in mounting, DVI-D port



NYM15W-C1060

Industrial Monitor, 15.4" display with capacitive touchscreen, Build-in mounting, NYML port



NYM19W-C1000

Industrial Monitor, 18.5" display with capacitive touchscreen, Build-in mounting, DVI-D port



NYM19W-C1060

Industrial Monitor, 18.5" display with capacitive touchscreen, Build-in mounting, NYML port



S8BA-24D24D240LF

UPS, DIN rail type, DC-DC, 10A, 240W



S8BW-C02

UPS Connection cable (CONTACT)



NY000-AK00

Spare part accessory kit (connectors, drive bracket, screws, etc)


Downloads

CAD Library



EAC Mark removal Discontinuation Notice

EN PDF 221 KB



Industrial PC Platform Brochure

EN PDF 5.26 MB



NY-series Industrial Box PC

Users Manual

EN PDF 8.53 MB



NY-series Operating Systems and Software Utilities Manual

Users Manual

EN PDF 2.25 MB



NYB Industrial Box PC Datasheet

EN PDF 2 MB



Panasonic BRxxxxA button cells

Battery Safety Datasheet

EN PDF 73.4 KB