


Decompose graphs and parameters

USB connector Two in four		(Interface Type-c, iphone, iphone, Apple Watch magnetic charge) Wired charging cable					
A process	1	Forming material: Aluminum alloy shell, circuit board, black and white nylon braided wire	C	1	Copper core wire:	Main line OD:3.8mm Secondary line OD:3.4mm Secondary line OD:2.8mm(Apple Watch Magnetic charge)	
	2	Wiring internal model black, red, green, white four-core cable		2	Mainline input power:	5V/3A	
	3	Cut line		3	Main line output power:	5V/3A	
	4	Solder joint plate		4	Branch output power:	5V/3A 15W (Max) Apple Watch Magnetic Charge (5V/0.6A 3W)	
	5	Plastic molding with aluminum alloy shell		5	colour:	Black and white matching	
B	1	Electrical performance	1. Contact impedance: 50mMax; 2. Resistance value of MOS tube: 25-35mQMax, 3. Anti-static $\geq 8000V$; 4. Anti-surge $\geq 80V$ 5. Working environment: $-30^{\circ}C-50^{\circ}C$; 6. Temperature resistance: welding $380^{\circ}C$, rubber material $260^{\circ}C$:				
	2	material	1. Shell: zinc alloy nickel-plated 100u ² ; 2. Gold finger: C2680 copper T=0.32MM, gold plated 3u ² : 3. Plastic core: white ABS 4.PCB board: FR-4, bending strength $\geq 8.Kgf$.				
	3	appearance	1. The shell has no scratch and no collapse: 2. The hardware terminal and the PC board are centered, without skew; 3. Solder plate, solder plate position and electronic components shall not exceed the edge of the plate. 4. Core: Main line OD:3.8mm Secondary line OD:3.4mm Secondary line OD:2.8mm(Apple Watch Magnetic charge)				
	4	Plug and pull test	30 times/min, 5000 times, normal function.				
	5	compatibility	Compatible with the highest system versions of all general-purpose models				
	6	Standard five-guard circuit	1. Anti-short circuit 2. Anti-high voltage 3. Anti-surge 4. Anti-backflow 5. Anti-static				
	7	weight	Net weight: 64g Gross weight: 80g Total weight: 24.8KG				
	8	Package size	Box 10.5*10.5*1.8CM Outer box 42*42*31.5CM 300/ box				
							
Part No : USBC-42-4		Product Name : USB Cable 4-in-2 Fast Multi Charging Nylon Braided Magnetic Cord 6 FT / 1.8 M, Black White			