

QUAD ROW TERMINAL/SOCKET

(1.27 mm) .050" PITCH • FOLC/MOLC SERIES



FOLC Board Mates: MOLC

MOLC Board Mates:

SPECIFICATIONS

Insulator Material: Black Liquid Crystal Polymer Contact Material (FOLC): Terminal Material (MOLC): Phosphor Bronze Plating: Au or Sn over 50 μ" (1.27 μm) Ni Current Rating: 2.6 A per pin (4 pins powered) Operating Temp Range: -55 °C to +125 °C -55 °C to +125 °C

Voltage Rating:
165 VAC/230 VDC
Insertion Depth (FOLC):
(3.30 mm) .130" to
(4.06 mm) .160"


PROCESSING

Lead-Free Solderable:

Max Cycles (FOLC):

SMT Lead Coplanarity (MOLC): (0.10 mm) .004" max (20-25) (0.15 mm) .006" max (30-50)* *(.004" stencil solution may be available; contact ipa@samtec.com)

APPLICATIONS



LEAD STYLE		MATED	
MOLC	FOLC	HEIGHT*	
-01		(5.97) .235	
-11	-01	(7.75) .305	
-31		(11.43) .450	

*Processing conditions will affect mated height.

Note:

Some lengths, styles and options are non-standard, non-returnable.





PER ROW

20, 25,

30, 35,

40, 45, 50

(Standard

sizes)


(5.59)

LEAD

-01 & -04= Through-hole

-M1 & -M2 = Mixed Technology

-L1 & -L4 = Low Insertion Force Through-hole



View complete specifications at: samtec.com?FOLC

PLATING

-L

= 10 µ"

(0.25 µm)

Gold on

contact, Matte Tin

on tail





OPTION

-LC

PACKAGING

Leave blank for tubes = Locking

Clip -TR (Manual = Tape & Reel placement required) (-MX only)

> -FR = Full Reel Tape & Reel (must order max. quantity per reel; contact Samtec for quantity breaks) (–MX only)



LEAD STYLE	С	
-01, -M1	(1.91) .075	
-04M2	(3.04) .120	



THROUGH-HOLE

MIXED

TECHNOLOGY

20, 25, 30, 35, 40, 45, 50 (Standard sizes)

> 0000000

No. of positions x (1.27) .050 + (2.54) .100 -

← No. of positions x (1.27) .050 + (0.76) .030 -

00000009

-'X'1 = Through-hole (Specify from chart)

-02 = Surface Mount -M1

= Mixed

Technology

(6.35) .250

(5.59) .220

-L= 10 µ" (0.25 µm) Gold on post, Matte

Tin on tail





= Locking

Clip (Manual placement

required)

-P = Pick & Place Pad

(-02 only)

MOUNT

ďν
-LC OPTION

bı (-	quantity reaks) -02 & I1 only)
A	В

for tubes

-TR

(-02 &

-M1 only)

-FR

= Full Reel

Tape & Reel

(must order

max. quantity

per reel; contact Samtec

Tape & Reel

View complete specifications at: samtec.com?MOLC

LEA STYL		A	В	
-01	(5.5	9) .220	(3.38) .133	
-11	(7.3	4) .289	(2 (() 4 4 4	
-31	(11.0)5) .435	(3.66) .144	

samtec.com/127mm-TigerEye