



Data Sheet AB2063BF-LW50


Features:

- Ultrathin and lightweight 20mm feedback bender
- 6,300 Hz resonant frequency
- Lead wires for easy installation

Specifications

Parameters	Values	Units	
Resonant Frequency	6,300 ± 600	Hz	
Resonant Impedance (Max)	800	Ohms	
Max Input Voltage	30	Vp-p	
Capacitance (@ 120 Hz)	8,500 ± 30%	pF	
Plate Material	Brass	-	
Storage Temperature	-30 ~ 80	°C	
Operating Temperature	-20 ~ 70	°C	
Environmental Compliances	RohS/Reach	Exempt. 7c-1	

Dimensions



This document contains data proprietary to PUI Audio Inc. Any use or reproduction, in any form, without prior written permission of PUI Audio Inc. is prohibited.

© 2024, PUI Audio Inc.

Packaging

100pcs/bag, paper box packaging

Specifications Revisions

Revision	Description	Date	Approved
Α	Released from Engineering	3/6/2024	JD

Note:

- 1. Unless otherwise specified:
 - A. All dimensions are in millimeters.
 - B. Default tolerances are ± 0.5 mm and angles are $\pm 3^{\circ}$.
- 2. Specifications subject to change or withdrawal without notice.