



Data Sheet AB4108A


### Features:


- Ultrathin and lightweight 31mm bender
- 800 Hz resonant frequency
- Low power consumption

# **Specifications**

Parameters	Values	Units
Resonant Frequency	800 ± 300	Hz
Resonant Impedance (Max)	600	Ohms
Max Input Voltage	30	Vp-p
Capacitance (@ 120 Hz)	75,000 ± 30%	pF
Plate Material	Alloy	-
Storage Temperature	-30 ~ 80	°C
Operating Temperature	-20 ~ 70	°C
Environmental Compliances	RohS/Reach	Exempt. 7c-1

### **Dimensions**





# **Packaging**

100pcs/roll, foam packaging 10 rolls/layer = 1000pcs total 5 layers = 5,000pcs

**Specifications Revisions** 

Revision	Description	Date	Approved
Α	Released from Engineering	3/7/2024	JD

### Note:

- 1. Unless otherwise specified:
  - A. All dimensions are in millimeters.
  - B. Default tolerances are ±0.5mm and angles are ±3°.
- 2. Specifications subject to change or withdrawal without notice.